



FEATURES AND BENEFITS

- Quick and easy installation
- Adhesive holds to surface during humidity exposure and hot/cold cycles
- RoHS-compliant
- Radiation direction maximized on adhesive side for outward-facing orientation
- Patent Number: 9450307
- Can be installed in the following ways:
 - On different non-conductive surfaces and thicknesses
 - On flat or curved surfaces
 - MIMO array element
 - On the front or top face of an enclosure interior (alternative placement to FlexPIFA)

SPECIFICATIONS

Frequency (MHz)	2400 - 2480
Peak Gain (dBi)	+3.1
Average Efficiency (dB)	> -2.1
VSWR (MHz)	< 2.5:1
Impedance (Ω)	50
Polarization	Linear

MECHANICAL SPECIFICATIONS

Antenna Type	Inverted Ground Flexible Planar Inverted F Antenna (i-FlexPIFA)	
Dimensions – mm (inches)	40.9 x 11.0 x 2.9 (1.61 x 0.43 x 0.114)	
Weight – g (oz.)	1.13 (0.040)	
Color	Clear yellow	
Adhesive	3M 100MP	
Connector Mating Height (max) – mm	MHF1 (U.FL)	2.5
	MHF4L	1.4

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature – °C (°F)	-40 to +85°C (-40 to +185°F)
Material Substance Compliance	RoHS

CONFIGURATION

PART NUMBER	CABLE LENGTH	CONNECTOR
EFG2400A3S-10MHF1	100 mm	MHF1
EFG2400A3S-10MH4L	100 mm	MHF4L

Note: Specifications are based on the 100mm cable length, standard antenna version with MHF1 / U.FL connector. Varying the cable length or type or connector will cause variations in these antenna specifications.

MECHANICAL DRAWING

Physical Dimensions (in mm) of the EFG2400A with a 100mm Long Cable




Figure 1: i-FlexPIFA mechanical drawing of EFG2400A Antenna

FLAT SURFACE ANTENNA MEASUREMENTS

Flat surface measurements were performed with the antenna centered on a 1.5 mm-thick plate of polycarbonate.

VSWR

i-FlexPIFA VSWR - 1.5mm PolyCarbonate




Figure 2: Antenna VSWR measured on a 1.5 mm-thick plate of polycarbonate with a nominal value of 1.45 across a sample size mounted on 1mm-3mm polycarbonate and both MHF1/MHF4L connector options

RETURN LOSS

S11, LOGMAG - i-FlexPIFA - 1.5mm PolyCarbonate




Figure 3: Antenna Return Loss measured on a 1.5 mm-thick plate of polycarbonate with a nominal value of -22.3dB

ANTENNA CHAMBER TEST SETUP

Antenna measurements such as VSWR and S11 were measured with an Agilent E5071C vector network analyzer. Radiation patterns were measured with a Rohde & Schwarz ZNB8-4PORT vector network analyzer in a Howland Company 3100 chamber equivalent. Phase center is nine inches above the Phi positioner.




Figure 4: Howland Company 3100 Antenna chamber

ANTENNA RADIATION PERFORMANCE

FlexPIFA centered on a 1.5 mm-thick plate of polycarbonate




Figure 5: Flat surface setup

EFFICIENCY




Figure 6: Antenna Efficiency measured on a 1.5 mm-thick plate of polycarbonate with a nominal value of -2.0dB across the operating frequency

ANTENNA GAIN










Figure 7: Antenna Gain measured on a 1.5 mm-thick plate of polycarbonate with a nominal value of 2.8dBi across the operating frequency

RADIATION PATTERNS – 2D Plots




2D Plots at 2400 MHz



2D Plots at 2440 MHz




2D Plots at 2480 MHz




RADIATION PATTERNS – 3D Plots

3D Plots at 2400 MHz

1) Radiation Pattern - Phi Polarization Gain at 2400 MHz



2) Radiation Pattern - Theta Polarization Gain at 2400 MHz



3) 3D Radiation Pattern - Total Gain at 2400 MHz






Figure 8: Phi polarization, Theta polarization and, and total gain plots – 2400 MHz

3D Plots at 2440 MHz

3D Radiation Pattern - Phi Polarization Gain at 2440 MHz



Radiation Pattern - Theta Polarization Gain at 2440 MHz



3D Radiation Pattern - Total Gain at 2440 MHz






Figure 9: Phi polarization, Theta polarization and, and total gain plots – 2440 MHz

3D Plots at 2480 MHz

3D Radiation Pattern - Phi Polarization Gain at 2480 MHz



Radiation Pattern - Theta Polarization Gain at 2480 MHz



3D Radiation Pattern - Total Gain at 2480 MHz




Figure 10: Phi polarization, Theta polarization and, and total gain plots – 2480 MHz

Rev 2.0 - Initial Production Release



ADDITIONAL ASSISTANCE

Please contact your local Laird Connectivity sales representative or our support team for further assistance:

Support Center <https://www.lairdconnect.com/resources/support>

Phone

Americas:	+1-800-492-2320
Europe:	+44-1628-858-940
Hong Kong:	+852 2762 4823

Web <https://www.lairdconnect.com/internal-antennas>

Address

Laird Connectivity
50 S. Main Street, Suite 1100
Akron, OH 44308

sales@lairdconnect.com
support@lairdconnect.com
www.lairdconnect.com

© Copyright 2023 Laird Connectivity. All Rights Reserved. Patent pending. Any information furnished by Laird Connectivity and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Connectivity materials or products rests with the end user since Laird Connectivity and its agents cannot be aware of all potential uses. Laird Connectivity makes no warranties as to non-infringement nor as to the fitness, merchantability, or sustainability of any Laird Connectivity materials or products for any specific or general uses. Laird Connectivity or any of its affiliates or agents shall not be liable for incidental or consequential damages of any kind. All Laird Connectivity products are sold pursuant to the Laird Connectivity Terms and Conditions of Sale in effect from time to time, a copy of which will be furnished upon request. Nothing herein provides a license under any Laird Connectivity or any third-party intellectual property right.