
Responsibility for Validation and Fitness-of-Use:

Because Valmark Industries, Inc. has no controlover the use or application of these parts, it is the sole responsibility of the OEM customer and/or its designated manufacturer to test all custom parts for fitness-of-use and validation of design prior to acceptance of production units. Valmark Industries provides expertise in the layout and consistent fabrication of high quality, reliable membrane switch, custom graphics and labeling products. Valmark and its employees do NOT purport to be experts in the end-use application of our customers, or the environments in which these products will be stored and/or used.

THIS PRINT MUST BE APPROVED AND RETURNED WITHIN 24 HOURS IN ORDER FOR THIS JOB TO PROCEED WITH PRODUCTION. ACCEPTANCE OF THE BELOW ART SAMPLE RELEASES VALMARK OF ANY GRAPHICS LIABILITY AFTER THE PRODUCTION RUN. (1) Valmark may, at its discretion unless otherwise noted, substitute any materials or BOM components with equivalent or similar materials and/or components based on control of cost or availability

Cust	tomer S	er Supplied Prints				
		Part Number	Date			
Dimensional Graphics Modification						
		ıs				
Rev.	ECO#	Description	Date			

DETAILED DIMENSIONS ARE IN THE CUSTOMER SUPPLIED DRAWING



RESUBMIT WITH CORRECTIONS	APPROVED WITH CORRECTIONS	OK AS IS	APPROVAL SIGNATURE	DATE
CORRECTIONS	CORRECTIONS	ON AG IS	SIGNATURE	DATE

NOTES:	CONSTRUCTION:
1 LABEL PERIPHERY-keyline does not print	.007" GE FR83-112
BACKGROUND: TRIMBLE MED. GREY NCS 5505-BO7G	ADHESIVE - FULL 3M 468
3 GRAPHICS: BLACK	
4 WHITE FOR OPACITY	

DO NOT S	CALE DRA	AWING	APPROVAL	S DATE	Valmark Interface Solutions
@		D ANGLE JECTION	DRW DW	07/11/14	
UNLESS OTHERWI	TOLERANCES:		CHK		
.XX ±0.01"	.XX ±0.01" .XX ±0.02" .XXX ±0.010" .XXX ±0.015" ANGLES ANGLES		DSN		COMPANY (OEM) TRIMBLE
ANGLES ±0.5°			ENGR		MANUFACTURERS:
INTERPRET DRAV ANSI Y14.5M -		SCALE 1:1	SHEI	ET 1 of 1	PART NO. 94469-00 REV ₀₁


Responsibility for Validation and Fitness-of-Use:

Because Valmark Industries, Inc. has no controlover the use or application of these parts, it is the sole responsibility of the CEM outsomer and/or its designated manufacture to test all custom parts for fitness-of-use and validation of design prior to acceptance of production units. Valmark Industries provides expertise in the layout and consistent fabrication of high quality, reliable membrane switch, custom graphics and labeling products. Valmark and its employees do NOT purport to be experts in the end-use application of our customers, or the environments in which these products will be stored and/or used.

THIS PRINT MUST BE APPROVED AND RETURNED WITHIN 24 HOURS IN ORDER FOR THIS JOB TO PROCEED WITH PRODUCTION. ACCEPTANCE OF THE BELOW ART SAMPLE RELEASES VALMARK OF ANY GRAPHICS LIABILITY AFTER THE PRODUCTION RUN. (1) Valmark may, at its discretion unless otherwise noted, substitute any materials or BOM components with equivalent or similar materials and/or components based on control of cost or availability

Customer Supplied Prints					
		Part Number	Date		
Dime	nsional				
Graphics					
Mod	ificatio	ns			
Rev. ECO#		Description	Date		

DETAILED DIMENSIONS ARE IN THE CUSTOMER SUPPLIED DRAWING



RESUBMIT WITH CORRECTIONS APPROVED WITH CORRECTIONS	OK AS IS	APPROVAL SIGNATURE	_ DATE
---	----------	-----------------------	--------

NOTES:	CONSTRUCTION:
1 LABEL PERIPHERY-keyline does not print	.007" GE FR83-112
BACKGROUND: TRIMBLE MED. GREY NCS 5505-B07G	ADHESIVE - FULL 3M 468
3 GRAPHICS: BLACK	
4 WHITE FOR OPACITY	

DO NOT S	CALE DRA	AWING	APPROVALS	DATE	Valmark Interface Solution		ano"
() ()		D ANGLE JECTION	DW	07/11/14		Kinetek Company	1112
UNLESS OTHERWIS ARE IN INCHES. T	OLERANCES:		СНК				
TOOLING: .XX ±0.01" .XXX +0.010"			DSN		COMPANY (OEM)	TRIMBLE	
ANGLES ±0.5°	ANGLES ±0.5°		ENGR		MANUFACTURER	S:	
INTERPRET DRAV ANSI Y14.5M -		SCALE 1:1	SHEET	1 of 1	PART NO. 9	4469-60	REV ₀₁


Responsibility for Validation and Fitness-of-Use:

Because Valmark Industries, Inc. has no controlover the use or application of these parts, it is the sole responsibility of the CBM outsomer and/or its designated manufacture to test all custom parts for fitness-of-use and validation of design prior to acceptance of production units. Valmark Industries provides expertise in the layout and consistent fabrication of high quality, reliable membrane switch, custom graphics and labeling products. Valmark and its employees do NOT purport to be experts in the end-use application of our customers, or the environments in which these products will be stored and/or used.

THIS PRINT MUST BE APPROVED AND RETURNED WITHIN 24 HOURS IN ORDER FOR THIS JOB TO PROCEED WITH PRODUCTION. ACCEPTANCE OF THE BELOW ART SAMPLE RELEASES VALMARK OF ANY GRAPHICS LIABILITY AFTER THE PRODUCTION RUN. (1) Valmark may, at its discretion unless otherwise noted, substitute any materials or BOM components with equivalent or similar materials and/or components based on control of cost or availability

Customer Supplied Prints					
		Part Number	Date		
Dime	nsional				
Graphics					
Mod	ificatio	ns			
Rev. ECO#		Description	Date		

DETAILED DIMENSIONS ARE IN THE CUSTOMER SUPPLIED DRAWING



RESUBMIT WITH CORRECTIONS APPROVED WITH CORRECTIONS	OK AS IS	APPROVAL SIGNATURE	_ DATE
---	----------	-----------------------	--------

NOTES:	CONSTRUCTION:
1 LABEL PERIPHERY-keyline does not print	BASE MATERIAL .007" GE FR83-112
BACKGROUND: TRIMBLE MED. GREY NCS 5505-B07G	ADHESIVE - FULL 3M 468
3 GRAPHICS: BLACK	
4 WHITE FOR OPACITY	

DO NOT S	CALE DRA	AWING	APPROVALS	DATE	Valmark Interface Solution		nno°
() ()		D ANGLE JECTION	DW	06/26/14		Kinetek Company)IIS
UNLESS OTHERWIS ARE IN INCHES. T	OLERANCES:		CHK				
TOOLING: .XX ±0.01" .XXX +0.010"			DSN		COMPANY (OEM)	TRIMBLE	
ANGLES ±0.5°	ANGLES ±0.5°		ENGR		MANUFACTURERS	S:	
INTERPRET DRAV ANSI Y14.5M -		SCALE 1:1	SHEET	Γ 1 of 1	PART NO. 94	1469-91	REV ₀₁