




Quick Guide

Magic Drawing Pad

Contents

English	01~04
---------------	-------

01. Product Overview



1. Power button
2. Volume button
3. Microphone
4. Micro SD card slot
5. USB Type-C port
6. Speakers
7. Front camera
8. Rear camera

02. Product Parameters

Product name	Magic Drawing Pad
Product model	9494 G
Operating system	Android 12
CPU	octa-core processor
Screen size	12.2 inches
Screen resolution	2160 x 1440
Screen authentication	TÜV Rheinland certified low blue light (Hardware solution)
Power input	9 V = 2 A or 5 V = 3 A
Battery capacity	8000 mAh
Storage	8 GB RAM + 256 GB ROM
Wireless connection	2.4GHz & 5GHz + Bluetooth 5.1
Product size	280.5 x 194.6 x 6.9 mm
Camera	8MP (front) , 13MP (rear)

03. Package contents

Drawing Pad	1 pc
TPU protective case	1 pc
Stylus	1 pc
Power adapter	1 pc
USB cable	1 pc
Pen nibs	8 pcs
Nib extractor	1 pc
Drawing glove	1 pc
Quick guide	1 pc
Warranty card	1 pc

Note:


Power adapter is not included in some areas, subject to actual package content.

04. Stylus




When replacing the pen nib, use the nib extractor to pinch the front end of the pen nib to pull out the old pen nib, and replace the new pen nib.

05. Charge & Insert or remove Micro SD card



As shown above, please use the included charger (if available) and USB cable for charging.

* Please fully charge the pad for the first time.



Please eject the tray using the included pin insertion tool provided and insert or remove the Micro SD card.

06. Important Safety information

Before using this device, please read all safety information to ensure proper and safe use.

- This device is composed of high-precision components, and users are forbidden to disassemble it by themselves. If the device fails, please contact the after-sales service in time for maintenance.

- This device is not waterproof. Please pay attention to moisture and water. If penetrated with water accidentally, do not turn up the device. Do not use any highly corrosive liquid to clean the parts of the device, if cleaning, please use neutral detergent and soft cleaning cloth.
- Please avoid the unit from falling from high places or under too much pressure. Do not touch the display with sharp objects to avoid scratching the display.
- Do not use, store or shake the device in high temperature, high pressure, strong static electricity, strong magnetic field or dusty environment, so as to avoid damage to the device.

Note:

If you need further service, please contact us.

Email: service@xp-pen.com

Website: www.xp-pen.com

FCC STATEMENT :

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference, and
- (2) This device must accept any interference received, including interference that may cause undesired operation.

Warning: Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules.

These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

Reorient or relocate the receiving antenna.

Increase the separation between the equipment and receiver. Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help.

The SAR limit adopted by FCC is 1.6 W/kg averaged over one gram of tissue. The highest SAR value reported to the FCC for this device type complies with this limit. The highest SAR value reported to the FCC for this device type when using in portable exposure conditions is 1.29 W/kg.

The device for operation in the band 5150-5250 MHz is only for indoor use to reduce the potential for harmful interference to co-channel mobile satellite systems

XPPEN TECHNOLOGY CO.

 service@xp-pen.com  www.xp-pen.com

Designed by XPPEN TECHNOLOGY CO. in California
Made in China