

12 FCC Warning

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:
(1) This device may not cause harmful interference, and
(2) This device must accept any interference received, including interference that may cause undesired operation.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference to other licensed operations. However, this equipment may cause interference to other licensed operations, especially radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment to an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

This equipment complies with FCC radiation exposure limits set forth for an uncontrolled environment. This equipment should be installed and operated with minimum distance 20cm between the radiator and your body.

11 IC Warning

This device complies with Industry Canada's Interference-Resistant (IR) classification. Operation is subject to the following two conditions:

- (1) This device may not cause interference, and
- (2) This device must accept any interference, including interference that may cause undesired operation of the device.

A product approved for sale in the United States and Canada is not necessarily approved for sale in other countries.

- (1) Repaired and/or replaced parts must be replaced with original equipment manufacturer (OEM) parts.
- (2) Repaired and/or replaced parts must be replaced with original equipment manufacturer (OEM) parts.

This device is a digital apparatus compliant with Canadian ICES-003.

Cet appareil numérique de la classe B est conforme à la norme NMB-003 du Canada.

IC-IR Statement:
When using the product, maintain a distance of 20cm from the body to ensure compliance with IC-IR requirements.

Déclaration IC-IR:
Lors de l'utilisation du produit, maintenez une distance de 20 cm de votre

corps afin d'assurer la conformité avec la norme NMB-003 du Canada.

09 Warranty Policy

Warranty Period: One Year. *The warranty period commences the date of purchase.
Shanghai Catlink Intelligent Technology Co., Ltd. warrants the device against defects in materials and workmanship under ordinary consumer use for one year from the date of original purchase.

Non-Warranty:

- 1- Damage caused by fire, flood, lightning, or other natural disasters.
- 2- Malfunctions caused by incorrect installation, improper use, or malicious tampering.
- 3- Damage caused by the use of third-party accessories.
- 4- Use of non-warranty period.
- 5- Damage caused by force majeure.
- 6- No valid proof of purchase.

10 Customer Service

We will provide customers with a one-year free warranty service.
If you have questions or need assistance, contact us!

Phone Support
+1 833 440 2772
+1 833 440 2772-6974 EST
Email: Support
support@catlink.cn 24/7

08 Detailed Hazard Data

Component	Hazardous Substances					RoHS Exemption (PBB)	RoHS Exemption (PBB)
	Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Hexavalent Chromium (Cr6+)	Polychlorinated Biphenyls (PCBs)		
Printed Circuit Board (PCB)	X	O	O	O	O	O	O
Plastic	O	O	O	O	O	O	O
Glass	O	O	O	O	O	O	O
Metal	O	O	O	O	O	O	O
Adhesive	O	O	O	O	O	O	O

This table is prepared in accordance with the provisions of EU Directive 2002/95/EC.

O: below the limit requirements specified in EU Directive 2002/95/EC.


X: above the limit requirements specified in EU Directive 2002/95/EC.

07 Product Information

Name	Catlink Smart Pet Drier
Model	C-60401, C-60402, C-60403, C-60404, C-60405, C-60406, C-60407, C-60408, C-60409
Main Material	ABS, Tempered Glass
Applicable	Cat or Small Dogs
Weight	5.1 kg
Standard	GB4706.1-2005, GB4706.19-2008
Dimensions	487 x 278 x 448 mm
Voltage	220 V
Power	1000 W
Operating Temperature	15 ~ 35 °C
Wireless Connection	Bluetooth
Version	V 1.0.1



SMART PET DRYER USER MANUAL




Please read carefully and keep this manual for
your reference.

01 Important Safety Instructions


Failure to comply with the following conditions may result in product malfunctions or unexpected damages.

- The drying function must only be used under the supervision of the user manual.
- If your pet has any physical or psychological health concerns, consult a professional veterinarian before using the device.
- Do not leave the device with your pet in reach.
- Keep items such as towels, pillows, or cushions away from the device to prevent air-went from getting blocked, which can affect temperature and airflow.
- Do not use the device on wet or damp surfaces.
- Place the device on a hard, cold surface, and avoid fluffy or soft objects.
- This device is suitable for cats (over 6 months) and small dogs.
- Do not use the device on animals with open wounds, skin diseases, or discomforts on the body.
- Contact the manufacturer immediately if you notice any unusual humming or unusual sounds from the device. When the device is not in use, turn it off and unplug it.
- Do not stack items on top of the device and keep both the interior and exterior clear and dry.
- Do not use the ozone disinfection function when pets are inside the device. Do not use the ozone disinfection function when maintaining to prevent pets from accidentally entering the device. Wait for 30 minutes after disinfection is completed before allowing pets to re-enter.
- Use the signal jumper next to prevent device damage or safety hazards.
- Leave a 10cm space when placing the device against a wall.
- Do not disassemble, modify, or attempt to attempt to repair the device on your own, as it may void all warranty and safety.
- For any doubts, feel free to contact customer service support.

02 Product



03 Buttons and Display



04 Operation Instructions

First-time Usage: Turn on the power switch. The default mode is Comfort Drying. After the device starts, the screen will show the current mode and temperature.

Mode Switch: After unlocking, press the pause button to stop, and press the Mode select button to switch drying modes.

Ozone Disinfection: After unlocking, press the on/off button and the Mode select button at the same time to start.

Customization: For Bluetooth version, personalize temperature, time, and speed settings through the app.

Temperature: -C / F

Time: 00:00

Mode Select: White - Running normally, Red - Operating abnormally

05 Installation and Usage

To ensure the safety of your pet and proper usage, the device is designed in its inactive state. Please download and install the CATLINK APP and follow the product instructions.

Scan QR code to access installation and usage instructions.

Scan to download CATLINK APP

06 Maintenance

Scan QR code to access maintenance instructions.

Scan to download CATLINK APP

This product complies with the radio interference requirements of the European Community.

Product name: Catlink smart pet dryer

Product model: C L - D A - 0 2

Manufacturer: Shanghai Catlink Intelligent Technology Co.,Ltd

Address: N o . 8 0 0 N a x i a n r o a d , P u d o n g n e w d i s t r i c t , S h a n g h a i , C h i n a

Frequency Range: 2402MHz to 2480MHz

Max. output Power: 1.26 **dbm**

SIMPLIFIED EU DECLARATION OF CONFORMITY

The simplified EU declaration of conformity referred to in Article 10(9) shall be provided as follows:

Hereby, [Shanghai Catlink Intelligent Technology Co., Ltd](#) declares that radio equipment type C L - D A - 0 2 is in compliance with Directive 2014/53/EU, and this product is allowed to be used in all EU member states.

The full text of the EU declaration of conformity is available at following

This product can be used across EU member states.