



ResMed

AirSense™ 10 AUTOSET

AUTOSET FOR HER

ENGLISH

FCC information

This document provides additional information regarding compliance of the AirSense 10 device with FCC Rules and Industry Canada license-exempt RSS standards.

FCC ID: 2ACHL-AIR10CD

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

- This device may not cause harmful interference,
- This device must accept any interference received, including interference that may cause undesired operation.

This device is designed and manufactured not to exceed the emission limits for exposure to radio frequency (RF) energy set by the Federal Communications Commission of the U.S. Government and Industry Canada.

The exposure standard employs a unit of measurement known as the Specific Absorption Rate, or SAR. The SAR limit relevant for the application described in the manual is 1.6W/kg. Tests for SAR are conducted using standard operating positions accepted by the FCC with the device transmitting at its highest certified power level in all tested frequency bands. Although the SAR is determined at the highest certified power level, the actual SAR level of the equipment while operating can be well below the maximum value. This is because the device is designed to operate at multiple power levels so as to use only the power required to reach the network. In general, the closer you are to a wireless base station antenna, the lower the power output.

Equipment Authorization has been granted to this model with the reported SAR level(s) evaluated as in compliance with the FCC RF exposure guidelines. SAR information on this equipment is on file with the FCC and can be found under the Display Grant section of www.fcc.gov/oet/ea/fccid after searching on the FCC ID as printed on the equipment.

This device has been tested to comply with FCC and IC radiation exposure limits set forth for an uncontrolled environment when used for the documented intended purpose and when mounted and operated as shown in the user guide. The device has been tested for a minimum distance of 20 mm between the device and the human body.

This device complies with the FCC radiation exposure limits set forth in an uncontrolled environment. This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna,
- Increase the separation between the equipment and receiver,
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected,
- Consult the dealer or an experienced radio/TV technician for help.

Any change or modification to the product is not expressly approved by Resmed and could void the user's authority to operate the device.

Industry Canada, IC: 9103A-AIR10CDMA

This device complies with Industry Canada license-exempt RSS standard(s). Operation is subject to the following two conditions:

- This device may not cause harmful interference,
- This device must accept any interference received, including interference that may cause undesired operation.

The device has been designed to comply with safety standards for exposure to radio waves (SAR) in accordance to RSS-102.