

Internal Photos


The following photos depict the internal construction of the Advance Trillium RFID reader (Model RH600102)



Assembled



Removed from housing



RFID reader circuit assembly (two circuit boards, soldered together), top





Reader board, front



Reader board, rear



Antenna board, front



Antenna board, rear

Wall Reader Control

Board (No RFID

Components)



Internal Photos

The following photos depict the internal construction of the Advance Trillium RFID wall reader (Model RH600103)








Cover removed from housing

RFID Reader

circuit assembly




Disassembled




RFID reader circuit assembly (two circuit boards, soldered together), top





Reader board, front



Reader board, rear



Antenna board, front



Antenna board, rear



Internal Photos

The following photos depict the internal construction of the Advance Trillium RFID wall reader (Model RH600103)




Display/Keypad Board

Encoder Control Board

Assembled


Cover removed from housing





RFID reader circuit assembly (two circuit boards, soldered together), top









Reader board, rear



Antenna board, front



Antenna board, rear



Internal Photos

The following photos depict the internal construction of the Trillium RFID reader (Model RH600101)



Assembled




Removed from housing




RFID reader circuit assembly (three circuit boards, soldered together), top







Reader board, front






Antenna board, front



Antenna board, rear



Flexible harness